



TS-877XU-RP-3600-8G		
CPU	AMD Ryzen™ 5 3600 6-core/12-thread processor, burst up to 4.2 GHz	
CPU Architecture	64-bit x86	
Floating Point Unit	Yes	
Encryption Engine	Yes (AES-NI)	
System Memory	8 GB UDIMM DDR4 (2 x 4GB)	
Maximum Memory	64 GB (4 x 16 GB)	
Memory Slot	4 x UDIMM DDR4	
Flash Memory	5GB (Dual boot OS protection)	
Drive Bay	8 x 3.5-inch SATA 6Gb/s, 3Gb/s	
Drive Compatibility	3.5-inch SATA hard disk drives 2.5-inch SATA hard disk drives 2.5-inch SATA solid state drives	
Hot-swappable	Yes	
SSD Cache Acceleration Support	Yes	
GPU pass-through	Yes	
Gigabit Ethernet Port (RJ45)	2	
10 Gigabit Ethernet Port	2 x 10GbE SFP+ SmartNIC port	
Wake on LAN (WOL)	Yes	
Jumbo Frame	Yes	
PCIe Slot	4 Slot 1: PCIe Gen 3 x4 Slot 2: PCIe Gen 3 x8 or PCIe Gen 3 x4* Slot 3: PCIe Gen 3 x4 Slot 4: PCIe Gen 3 x8 or PCIe Gen 3 x4**	
USB 3.2 Gen 1 port	4	

USB 3.2 Gen 2 (10Gbps) Port	1 x Type-C USB 3.2 Gen 2 10Gbps 1 x Type-A USB 3.2 Gen 2 10Gbps
Form Factor	2U Rackmount
LED Indicators	HDD 1-8, Status, LAN, storage expansion port status
Buttons	Power, Reset
Dimensions (HxWxD)	88.3 × 482 × 562 mm
Weight (Net)	13.31 kg
Weight (Gross)	15.46 kg
Operating temperature	0 - 40 °C (32°F - 104°F)
Storage Temperature	-20 - 70°C (-4°F - 158°F)
Relative Humidity	5-95% RH non-condensing, wet bulb: 27°C (80.6°F)
Power Supply Unit	300W (x2), 100-240V
Power Consumption: Operating Mode, Typical	86.04 W
Fan	System fan: 2 x 70mm, 12VDC
System Warning	Buzzer
Max. Number of Concurrent Connections (CIFS) - with Max. Memory	3500

Note: Use only QNAP memory modules to maintain system performance and stability. For NAS devices with more than one memory slot, use QNAP modules with identical specifications.

 $Warning: Using \ unsupported \ modules \ may \ degrade \ performance, \ cause \ errors, \ or \ prevent \ the \ operating \ system \ from \ starting.$ 

Environment: Refer to ISO 7779; Maximum HDD loaded; Bystander Position; Average data from 1 meter in front of operating NAS. Product images are for illustrative purposes only and may differ from the actual product. Due to differences in monitors, colors of products may also appear different to those shown on the site.

Designs and specifications are subject to change without notice.

<sup>\*</sup> Sound Level Test