



## APC Replacement Battery Cartridge #5 with 2 Year Warranty

RBC5

Call for More Information

- Includes: All required connectors, Battery recycling guide, Installation guide, Reusable packaging

Output	
Battery Capacity (mAh)	7000
Battery Output Voltage	24 V

  

Batteries & Runtime	
Battery type	Lead-acid battery
Expected Battery Life (years)	3 - 5
RBC Quantity	1

  

Physical	
Maximum Height	94MM, 9.4CM
Maximum Width	130MM, 13.0CM
Maximum Depth	150MM, 15.0CM
Net Weight	4.96KG
Shipping weight	5.46KG
Shipping Height	168MM, 16.8CM
Shipping Width	224MM, 22.4CM
Shipping Depth	168MM, 16.8CM
Color	Black

  

Environmental	
Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 %

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

Environmental	
Operating Elevation	0 - 3048meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0 - 15240meters

Conformance	
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant
PEP	Available in Documentation tab
EOLI	Available in Documentation tab
Proposition 65 Warning	Available in Documentation tab

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.