

Infra Red R125 E27 250W Red Hard Glass

Article number RI7125240250R

VIC IR Reflector R125 E27 240V 250W Red Halogen 126x185mm Infra Red lamp

Using special (clear/red) doped borosilicate glass there is no need to use potentially hazardous lacquers. Applications: Catering, Agricultural, Paint drying, Personal care.



General ETIM properties

| | |
|---------------|---------------------|
| ETIM group | Lamps |
| ETIM class | IR lamp |
| Name | RI7125240250R |
| Brand | VICTORY |
| Productseries | Infra red reflector |
| Product type | R125 |

ETIM specifications

| | |
|---|-----------------------|
| Weighted energy consumption in 1000 hours [kWh] | 250 |
| Average nominal lifespan [h] | 5000 |
| Diameter lamp [mm] | 126 |
| Total length [mm] | 185 |
| Dimmable | Yes |
| Lamp power [W] | 250 |
| Lamp voltage [V] | 220 - 240 |
| Socket | E27 |
| Lamp shape | R-butt/reflector lamp |
| Lamp type | Incandescent lamp |

Alternative articles



60800122350

BR125 IR 250W E27
230-250V Red