



## Infra Red R125 E27 250W Clear Hard Glass

Article number RI7127240250

VIC IR Hard Glass Reflector R125 E27 240V 250W Clear Halogen 125x180mm Infra Red lamp

Using special (clear/red) doped borosilicate glass there is no need to use potentially hazardous lacquers. Applications: Catering, Agricultural, Paint drying, Personal care.

### General ETIM properties

|               |                     |
|---------------|---------------------|
| ETIM group    | Lamps               |
| ETIM class    | IR lamp             |
| Name          | RI7127240250        |
| Brand         | VICTORY             |
| Productseries | Infra red reflector |
| Product type  | R125                |

### ETIM specifications

|   |                       |
|---|-----------------------|
| Weighted energy consumption in 1000 hours [kWh] | 250                   |
| Average nominal lifespan [h]                    | 5000                  |
| Diameter lamp [mm]                              | 125                   |
| Total length [mm]                               | 180                   |
| Dimmable  | Yes                   |
| Lamp power [W]                                  | 250                   |
| Lamp voltage [V]                                | 220 - 240             |
| Socket  | E27                   |
| Lamp shape                                      | R-butt/reflector lamp |
| Lamp type                                       | Incandescent lamp     |

**Alternative articles**



60800122044

BR125 IR 250W E27  
230-250V CL