

Glass Fuse Kit

Fast-blow, 5x20 mm, 360 pcs



SPECIFICATION:

Rated Current	0.1 ~ 30A
Quantity	360 pcs
Size	5 x 20 mm
Voltage Rating - AC	250 V
Fuse Characteristic	Fast Blow

MATERIAL:

Fuse Body	Glass tube
Ferrule Cap	Brass, nickel-plated

ELECTRICAL CHARACTERISTICS:

Relative Humidity	15°C ~ 35°C
Air Pressure	8.6 × 10Pa ~ 1.06 × 10Pa

TIME/CURRENT CHARACTERISTIC OPENING TIME:

Rating		Blowing Time	
		32-100mA	125mA & OVER
2.11n	Max	30min	30min
	Min	10ms	50ms
2.751n	Max	500ms	2s
	Min	3ms	10ms
41n	Max	100ms	300ms
	Min	20ms	20ms

INCLUDED:

Values	pcs	Values	pcs
100mA	20	800mA	20
125mA	20	1A	20
160mA	20	1.25A	20
200mA	20	1.6A	20
250mA	20	2A	20
315mA	20	2.5A	20
400mA	20	3.15A	20
500mA	20	4A	20
630mA	20	6.3A	20

Art. Nr.**RND 170-00193**