

Glass Fuse Kit

Slow-blow, 5x20 mm, 100 pcs



SPECIFICATION:

Rated Current	0.1 ~ 30A
Quantity	100 pcs
Size	5 x 20 mm
Voltage Rating - AC	250 V
Fuse Characteristic	Slow Blow

MATERIAL:

Fuse Body	Glass tube
Ferrule Cap	Brass, nickel-plated

ELECTRICAL CHARACTERISTICS:

Relative Humidity	15°C ~ 35°C
Air Pressure	8.6 × 10Pa ~ 1.06 × 10Pa

TIME/CURRENT CHARACTERISTIC OPENING TIME:

RATING	BLOWING TIME
110%	4 Hours Min
135%	1 Hour Max
200%	120 Sec Max

INCLUDED:

Values	pcs	Values	pcs
1A	10	3.15A	10
1.25A	10	4A	10
1.6A	10	5A	10
2A	10	6.3A	10
2.5A	10	10A	10

Art. Nr.
RND 170-00194