

Coaxial D-Sub Combination Connector 8W8



SPECIFICATION:

Signal contacts	0 p.
Special contacts	8 p.
Termination	Solder Cup / Solder Lug/Straight
Gender of contacts	Male
Contact material	Brass
Housing Material	Steel/Tin-Plated/Nickel (Ni)
Insulator	PBT
Temperature range	-55...+105 °C

Art. Nr.

RND 205-00758

Associated pin contacts:

30100395 RND 205-00731, Male power pin, solder, 10A

30100396 RND 205-00732, Male power pin, solder, 20A

