

Rotary DIP switch

HEX 3+3



Flush type

With screwdriver slot

IP 67 protection

SPECIFICATION:

Switching type	HEX
Row spacing	5.08 mm
Pins	3+3
Actuation	side
Switching capacity	100 mA@ 42 V
Contact resistance	<80 mΩ
Contact material	Gold-plated
Test voltage	250 VAC
Temperature range	-60...+125 °C

Art. Nr.

RND 210-00142

		Real Coded				
		C	1	2	4	8
10 P o s i t i o n	0	●				
	1	●	●			
	2	●		●		
	3	●	●	●		
	4	●			●	
	5	●	●		●	
	6	●		●	●	
	7	●	●	●	●	
	8	●				●
	9	●	●			●
16 P o s i t i o n	A	●		●		●
	B	●	●	●		●
	C	●			●	●
	D	●	●		●	●
	E	●		●	●	●
	F	●	●	●	●	●

