

# AC-DC Switching Adapter

## 12 W, Euro plug



### FEATURES:

With over voltage, over current and over power protection

L.P.S (Limits for power source)

### SPECIFICATION:

Output voltage	12 VDC
Power	12 W
Connection, primary side	Euro plug
Connection, secondary side	2.1 x 5.5 x 12 mm Barrel plug
Input voltage	100...240 VAC
MTBF	50 000 Hours min
Output current	0...1 A
Cable Length	1.8 m
Dimensions L x W x H	76.5 x 42.4 x 72.2 mm
Input frequency	50...60 Hz
No load power consumption	< 0.3 W
Line regulation	0.5 %
Operating temperature max.	25 °C
Operating temperature min.	0 °C
Short-circuit-proof	Yes
Weight	110 g
Appliance	Class II
Efficiency	CEC-400-2006-002-REV1 Efficiency level V



Art. Nr.

RND 320-00025

