

Type K Thermocouple

Features

- M8x1 threaded pot seal with locknuts
- Highly flexible sheath
- Bendable to suit many applications and processes
- Insulated hot junction



Specification

Cable Length	1 m
Insulation Material	PTFE
Sensor Type	K
Thermocouple Material	NiCr / NiAl
Probe Material	Stainless Steel
Probe Length	300 mm
Probe Diameter	3 mm
Conductors	7
Conductor Cross-Section	0.2 mm ²
Cable Type	Twisted Pair
Temperature Range	-40 ... 1100 °C
Rated Connection Temperature	200 °C

Art. Nr.
RND 410-00165