Miniature Panel Mount Thermocouple Connector



Features


- Stainless steel bracket simply fitted to connector
- Fully enclosed terminals with cable port seal
- Reliable thermocouple connection for accurate temperature measurements



Specification

Sensor Type	Т	
Connector Size	Miniature	
Connector Type	Socket with SS Bracket	
Colour	Brown	
Max. Temperature	220 °C	
+Positive Contact	Cu	
-Negative Contact	CuNi	
Standards Met	BS EN 50212:1997; RoHS	

Drawing



Miniature in-line Socket with stainless steel mounting bracket (dimensions in mm)

Art. Nr. RND 410-00196