

# 4 Wire Class B Resistance Thermometer



## Features

- Heavy duty Pt100 probe with terminal head
- IP67 aluminium alloy weatherproof connection head
- This sensor employs a 4-wire configuration, minimizing lead wire resistance effects for more accurate temperature readings



## Specification

Sensor Type	Pt100
Head Type	KNE
Termination Type	4 Wire Connection Block
Probe Length	200 mm or 400 mm
Probe Diameter	6 mm
Max. Temperature	450 °C (Connection Head @ 170 °C)
Min. Temperature	-50 °C
IP Rating	IP67
Accuracy	Class B

## Product Range

Probe Diameter	Probe Length	Code
6 mm	200 mm	RND 410-00281
6 mm	400 mm	RND 410-00282