

Mineral Insulated General Purpose Probe Type K



Features

- 316 Stainless Steel Air Probe with a vented sheath for general air temperature
- Suitable for use in various environments, including industrial settings and food applications
- Designed with a sharp, pointed tip, the probe is ideal for inserting into solids, liquids, and semi-solids to accurately measure their internal temperatures



Specification

Sensor Type	K
Probe Tip Type	Rounded Tip
Probe Diameter	1.5 mm or 3 mm
Probe Length	100 mm or 300 mm
Cable Length	2 m
Cable Material	Polyurethane
Cable Termination	Mini Plug
Maximum Temperature Measurement	850 °C

Product Range

Dia x Length

1.5 mm x 100 mm

3 mm x 300 mm

Code

RND 410-00318

RND 410-00319