

Thermocouple Surface Probe Type K

Features

- Stainless steel sheath with a molded handle and 2 m of coiled extension cable terminated in a miniature thermocouple plug
- This surface probe is equipped with a flat, sensitive tip designed for direct contact with surfaces
- Built with robust materials, this probe is designed to withstand the rigors of industrial environments



Specification

Sensor Type	K
Probe Tip Type	Surface Tip
Probe Diameter	15 mm
Probe Length	170 mm
Cable Length	2 m
Cable Material	Polyurethane
Cable Termination	Mini Plug
Maximum Temperature Measurement	400°C

Art. Nr.

RND 410-00324