

# Resistance Thermometer with Compact KNS Head



## Features

- The Pt100 sensor, known for its accuracy and stability, ensures precise temperature readings
- The KNS head provides a protective housing for the sensor, ensuring durability in demanding environments
- It meets stringent accuracy requirements, making it suitable for applications where precise temperature control is essential



## Specification

Sensor Type	Pt100 (100 Ohms @ 0°C) to IEC 751
Probe Material	316SS
Cable Termination	IP67 KNS Connection Head
Process Connection Cable	Stainless Steel Plug
Entry	M16 x 1.5 mm
Probe Temperature Range	-50 °C to 450 °C

## Order Codes

Probe DiaØ	Probe Length	Order code
6 mm	100 mm	RND 410-00329