

Brushless Axial DC Fan

40 x 40 x 10 mm, 24 V, 1.68 W



FEATURES:

Single impeller fan with low noise characteristics

Suitable for most applications

SPECIFICATION:

Dimensions	40 x 40 x 10 mm
Rated voltage	24 V
Rated current	0.07 A
Volumetric flow rate max.	21 m ³ /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	37.3 dBA
Power consumption	1.68 W
Revolution speed	10000 rpm
Temperature range	-10...+70 °C
Voltage	14.0...26.4 V
Weight	20 g
Max. air flow	0.35 m ³ /min 12.23 CFM
Max. static pressure	8.43 mm-H ₂ O 0.33 In-H ₂ O



Art. Nr.

RND 460-00003

