

Brushless Axial DC Fan

60 x 60 x 15 mm, 12 V, 2.88 W



FEATURES:

Single impeller fan with low noise characteristic

Suitable for most application

SPECIFICATION:

Dimensions	60 x 60 x 15 mm
Rated voltage	12 V
Rated current	0.12 A
Volumetric flow rate max.	42.9 m ³ /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	35 dBA
Power consumption	1.44 W
Revolution speed	4500 rpm
Temperature range	-10...+70 °C
Voltage	7.0...13.2 V
Weight	44 g
Max. air flow	0.65 m ³ / m in 23.10 CFM
Max. static pressure	4.60 mm-H ₂ O 0.18 In-H ₂ O



Art. Nr.

RND 460-00009

