

Brushless Axial DC Fan

60 x 60 x 20 mm, 12 V, 1.56 W



FEATURES:

Single impeller fan with low noise characteristic

Suitable for most application

SPECIFICATION:

Dimensions	60 x 60 x 20 mm
Rated voltage	12 V
Rated current	0.13 A
Volumetric flow rate max.	30.6 m ³ /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	31 dBA
Power consumption	1.56 W
Revolution speed	4400 rpm
Temperature range	-10...+70 °C
Voltage	7.0...13.2 V
Weight	50 g
Max. air flow	0.51 m ³ /min 18.10 CFM
Max. static pressure	5.80 mm-H ₂ O 0.23in-H ₂ O



Art. Nr.

RND 460-00012

