

Brushless Axial DC Fan

60 x 60 x 25 mm, 12 V, 4.80 W



FEATURES:

Single impeller fan with low noise characteristic

Suitable for most application

SPECIFICATION:

Dimensions	60 x 60 x 25 mm
Rated voltage	12 V
Rated current	0.4 A
Volumetric flow rate max.	74.4 m ³ /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	56 dBA
Power consumption	4.80 W
Revolution speed	6800 rpm
Temperature range	-10...+70 °C
Voltage	7.0...13.2 V
Weight	57 g
Max. air flow	1.24 m ³ /min 43.80 CFM
Max. static pressure	14.20 mm-H ₂ O 0.56 In-H ₂ O



Art. Nr.

RND 460-00015

