

# Brushless Axial DC Fan

80 x 80 x 20 mm, 12 V, 2.88 W



## FEATURES:

Single impeller fan with low noise characteristics

Suitable for most applications

## SPECIFICATION:

Dimensions	80 x 80 x 20 mm
Rated voltage	12 V
Rated current	0.24 A
Volumetric flow rate max.	69 m <sup>3</sup> /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	36 dBA
Power consumption	2.88 W
Revolution speed	3400 rpm
Temperature range	-10...+70 °C
Voltage	7.0...13.2 V
Weight	76 g
Max. air flow	1.15 m <sup>3</sup> /min 40.50 CFM
Max. static pressure	4.50 mm-H <sub>2</sub> O 0.18 In-H <sub>2</sub> O



Art. Nr.

RND 460-00022

