

Brushless Axial DC Fan

80 x 80 x 25 mm, 12 V, 2.76 W



FEATURES:

Single impeller fan with low noise characteristics

Suitable for most applications

SPECIFICATION:

Dimensions	80 x 80 x 25 mm
Rated voltage	12 V
Rated current	0.23 A
Volumetric flow rate max.	78.6 m ³ /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	36 dBA
Power consumption	2.76 W
Revolution speed	3600 rpm
Temperature range	-10...+70 °C
Voltage	7.0...13.2 V
Weight	76 g
	1.31 m ³ /min
Max. air flow	46.14 CFM
	5.45 mm-H ₂ O
Max. static pressure	0.21 In-H ₂ O



Art. Nr.

RND 460-00026

