

Brushless Axial DC Fan

120 x 120 x 25 mm, 12 V, 2.40 W



FEATURES:

Single impeller fan with low noise characteristics

Suitable for most applications

SPECIFICATION:

Dimensions	120 x 120 x 25 mm
Rated voltage	12 V
Rated current	0.2 A
Volumetric flow rate max.	132.6 m ³ /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	31 dBA
Power consumption	2.40 W
Revolution speed	2200 rpm
Temperature range	-10...+70 °C
Voltage	7.0...13.2 V
Weight	152 g
	2.21 m ³ /min
Max. air flow	78.20 CFM
	4.50 mm-H ₂ O
Max. static pressure	0.18 In-H ₂ O



Art. Nr.

RND 460-00032

