

# Standard Panel Mount Thermocouple Connector



## Features


- Intended for use in more industrial processes but can be used in all
- Easy 'jab-in' connection for rapid termination
- Just push wire in and tighten screw



## Specification

Sensor Type	K
Connector Size	Standard
Connector Type	Quick Wire Socket with SS Bracket
Colour	Yellow
Max. Temperature	220°C
+Positive Contact	NiCr
-Negative Contact	NiAl
Standards Met	BS EN 50212:1997; RoHS

## Drawing



**Standard Socket - Quick Wire with stainless steel mounting bracket**  
(dimensions in mm)

Art. Nr.  
RND 410-00204