LED Strip



Features

- No UV or IR light radiation
- RoHS compliant
- Easy Installation
- Long lifetime: 25000 hours (L70)
- Energy cost savings: over 60% compared to incandescent
- Solid-state: high-shock & high-vibration resistant, both electrical and mechanical
- Eco-friendly: no mercury, no lead content
- No hazardous emissions: no UV or IR radiation
- Constant light output: even lighting, non-halation


Applications

- Advertisement signboard lighting
- Exhibition stand lighting
- Showcase lighting
- Jewelry lighting
- Club lighting
- Bar lighting
- Other lighting

Specification

Input Voltage	24 VDC
Wattage	4.8 W/m
Operating Frequency	50 60 Hz
Operating Temperature	-20 50 °C
Storage Temperature	-30 70 °C
Beam Angle	120°
LED Type	3528
Total Lumens	320 lm/m ± 10%
Colour Temperature	4000 K ± 10%
LED Colour	Neutral White
CRI	≧ 70
Number of LEDs	60 per Meter
Waterproof Grade	IP20

Drawing



Notes:

- 1. All dimensions unit in mm
- 2. Tolerances is ±1mm unless otherwise noted.



Art Nr. RND 135-00269

