
Wafer 1 x 5P Male





FEATURES:

Poles	1 x 5	
Connector Design	Single row/straight	
Pitch	2.54 mm	
Gender of contacts	Male	
Connector Termination	straight	
Rated voltage	250 VAC	
Colour	beige	
Housing Material	Nylon 66	
Temperature range	-25+85 °C	





DRAWING:






RECOMMENDED P.C.BOARD HOLE DIMM.







D I	Dimension mm (in.)	
Poles	Α	B
2	2.54(0.100)	5.12(0.202)
3	5.08(0.200)	7.66(0.302)
4	7.62(0.300)	10.20(0.402)
5	10.16(0.400)	12.74(0.502)
6	12.70(0.500)	15.30(0.602)
7	15.24(0.600)	17.94(0.706)
8	17.78(0.700)	20.48(0.806)
9	20.32(0.800)	23.02(0.906)
10	22.86(0.900)	25.58(1.007)
11	25.40(1.000)	28.12(1.107)
12	27.94(1.100)	30.68(1.208)
13	30.48(1.200)	33.10(1.303)
14	33.02(1.300)	35.80(1.409)
15	35.56(1.400)	38.34(1.509)
16	38.10(1.500)	40.94(1.612)
17	40.64(1.600)	43.30(1.705)
18	43.18(1.700)	45.90(1.807)
20	48,26(1,900)	50,80(2,000)

Art. Nr. RND 205-00674