

# D-Sub Crimp Connector

50P, Female



## SPECIFICATION:

Poles	50
Termination	Straight/Crimp
Rows	3
Gender of contacts	Female
A	67 mm
B	61 mm
C	52.3 mm
Colour	Black
D	15.3 mm
E	10.9 mm
Housing Material	Steel
Insulator material	PBT
Outside material	Metal
Temperature range	-55...+105 °C
Rated current	3 A
Rated voltage	125 V
Proof voltage	1000 VAC

## Art. Nr.

**RND 205-00745**

Associated pin contacts:

30108938, RND 205-00787, Crimp Contacts, Female, 18...22 AWG

30108939, RND 205-00788, Crimp Contacts, Female, 24...26 AWG

