

# D-Sub Connector

## 25P, Male



### SPECIFICATION:

Poles	25
Termination	90°/Solder PCB THT
Gender of contacts	Male
A	53.05 mm
B	47.05 mm
C	38.95 mm
Colour	Black
Contact material	Brass, Gold-Flashed
D	12.5 mm
E	8.3 mm
Housing Material	Steel/Nickel-Plated
Insulator material	PBT
Outside material	Metal
Rated current	3 A
Temperature range	-55...+105 °C

Art. Nr.

RND 205-00773

