

USB Type A Male Solder Connector

4P



SPECIFICATION:

Poles	4
Housing material	Steel, UL 94 V-0
Temperature range	-55 ... +85 °C
Rated current	1.5 A
Contact material	Brass, Gold-Flashed
Dielectric withstand voltage	500 VAC
Insulation resistance	1000 MΩ min.
Contact resistance	30 mΩ max.

Art. Nr.

RND 205-00860

