

D-Sub to IDC Connector

25P



SPECIFICATION:

Poles	25
Insulator	PBT, UL 94 V-0
Gender of contacts	Male
Connection A	D-SUB 25-Pin Male
Connection B	IDC
Housing material	Steel
Temperature range	-45 ... +85 °C
Rated current	3 A
Contact material	Brass, Gold-Flashed
Dielectric withstand voltage	AC 1000 V RMS
Insulation resistance	500 MΩ min. at DC 500 V
Contact resistance	25 mΩ max.
A	53 mm
B	47 mm
C	38.8 mm
D	40.3 mm

Art. Nr.

RND 205-00867

