

HD D-Sub Connectors, Solder



Specification

Current Rating	3A
Contact Resistance	25mOhm max
Insulation Resistance	500MOhm min at DC 500V
Dielectric Withstanding Voltage	1000VAC
Operating Temperature	-55°C to 105°C
Insulator Material	PBT UL94V-0
Contact Material	Brass
Shell	Cold Rolled Steel
Contact Plating	Gold Flash
Gender	Plug

Product Range:

	Connector Size	Dimension A	Dimension B	Dimension C	Dimension D	Dimension E
RND 205-00997	DE-15	30.8 mm	25 mm	16.9 mm	12.5 mm	2.29 mm
RND 205-00998	DA-26	39.2 mm	33.3 mm	25.25 mm	12.5 mm	2.29 mm
RND 205-00999	DB-44	53.05 mm	47.05 mm	38.95 mm	12.5 mm	2.29 mm
RND 205-01000	DC-62	69.4 mm	63.5 mm	55.4 mm	12.5 mm	2.41 mm

