

Quick-Connect Terminal Block



Features

- Anti-creeping
- Anti-flaming & high-temperature resistance material
- Safer & easier install and operate



Mechanical Specification

Connection Capacity	0.2 ... 4 mm ² / 24 ... 12 AWG (Solid or Stranded Wire)
Stripping Length	11 mm
Number of Positions	2
Operating Temperature	-40 ... 70 °C

Electrical Specification

Voltage Rating	UL 600 V, IEC 450 V
Current Rating	32 A
Contact Resistance	20 mOhm max.
Insulation Resistance	500 MOhm, 500 V DC
Withstanding Voltage	3.4 kV AC, 1 min.

Material Specification

Body Material	Polycarbonate
Spring Clip	SUS 301
Conductor Material	Copper, Tin Plated
Cover Material	Polycarbonate

Drawing



Art. Nr.
RND 205-01242