

USB Connector



Features

- Plug & Play capability
- Gold plated contacts
- Typical applications would include smartphones, tablets, PCs and cameras



Specification

Current Rating	1 A
Dielectric Withstanding Voltage	100 VAC for 1 min.
Contact Resistance	50 mOhm Max.
Insulation Resistance	100 MOhm min.
Temperature Range	-25 ... 80 °C
USB Connector Type	Micro USB-B
USB Standard	USB 2.0
Gender	Receptacle

Material Specification

Housing	High Temperature Thermoplastic
Contact	Copper Alloy
Shell	Copper Alloy
Contact Finish	Gold Flash
Shell Finish	Nickel

Drawing

