

USB Connector



Features

- Plug & Play capability
- Gold plated contacts
- Typical applications would include smartphones, tablets, PCs and cameras



Specification

Current Rating	1.5 A
Dielectric Withstanding Voltage	500 VAC
Contact Resistance	30 mOhm Max.
Insulation Resistance	1000 MOhm min. @ 500 VDC
Temperature Range	-55 ... 85 °C
USB Connector Type	USB-B
USB Standard	USB 2.0
Gender	Plug

Material Specification

Contact	Brass
Insulator	PBT
Shell	SPCC
Contact Finish	Gold Flash
Shell Finish	Nickel

Drawing

