

# HDMI Connector



## Features

- RoHS compliant
- Compact and robust design
- Reliable wire-to-board connection for HDMI applications
- SMT Contact Pads with Through Hole mounting for the shell



## Specification

Current Rating	500 mA per Pin
Contact Resistance (Low Level)	30 mOhm max.
Insulation Resistance	100 MOhm min. @ 500 VDC
Dielectric Withstanding Voltage	300 VAC - Mate Connectors 500 VAC - Unmate Connectors
Operating Temperature	-25 ... 85 °C

## Material Specification

Housing	LCP, Black
Terminal	Copper Alloy
Shell	Copper Alloy
Contact Finish	Gold Flash
Shell Finish	Nickel

## Drawing

