# TNC to TNC Adapter



### **Features**


- Nickel-Plated brass body
- Commonly used in applications requiring 2 dissimilar RF interfaces to be connected
- RoHS compliant



### **Specification**

| Colour                          | Silver     |
|---------------------------------|------------|
| Impedance                       | 50 Ω       |
| Adapter Type                    | Angled     |
| Connector Type A                | TNC Plug   |
| Connector Type B                | TNC Jack   |
| Frequency Range                 | 0 4 GHz    |
| Voltage Rating                  | 500 V      |
| Dielectric Withstanding Voltage | 1.5 kV RMS |

### **Drawing**



## **Material Specification**

| Body      | Brass, Nickel Plated |
|-----------|----------------------|
| Contact   | Brass, Gold Plated   |
| Insulator | POM                  |
| Shell     | Brass, Nickel Plated |

Art. Nr. RND 205-01488