

Female Headers

7.62mm pitch



SPECIFICATION:

Material

Screws	M3.0 Steel, Zinc Plated
Wire Guard	Brass, Ni Plated
Housing	PA66, UL94V-0
Clamp	Phosphor Bronze, Ni Plated

Electrical

Standard	IEC	
Rated Voltage	300V	450V
Rated Current	15A	17.5A
Wire Range	28-14AWG	0.08-2.5mm ²
Contact Resistance	20mΩ	
Insulation Resistance	500MΩ/DC500V	
Withstand Voltage	AC2000V/1Min	

Mechanical

Temperature Range	-40°C~+105°C
Torque	0.5Nm(4.5Lb.in)
Strip Length	7-8mm

Size

Pitch	7.62mm (.300")
Poles	2P-6P

