

DIP switch

8P




FEATURES:

- Electrical life 2,000 operations
- Switching rating 25mA, 24VDC
- Soldering temperature 260°C for 5±1sec
- With top tape seal

SPECIFICATION:

Poles	8
Pitch	2.54 mm
Actuation	above
Contact resistance	50 mΩ
Contact material	Phosphor bronze
Test voltage	500 VAC
Temperature range	-20...+70 °C



Art. Nr.

RND 210-00166

