

SPECIFICATIONS:

BUSHING: \varnothing 19mm.
 CONTACT RATING: 5A @ 250VAC.
 ELECTRICAL LIFE: 50,000 cycles at full load.
 CONTACT RESISTANCE: 50m-ohms max. initial @2-4VDC.
 INSULATION RESISTANCE: 1,000M-ohms min.@500VDC.
 DIELECTRIC STRENGTH: 2,000V RMS 50~60Hz.
 IP CLASS: IP67 protection.
 TORQUE: 0.6Nm max. applied to nut.
 OPERATING FORCE: 4N max.
 CONSTRUCTION FORM: SPDT.
 SWITCHING CIRCUIT: ON-MOM.
 CONTACTS: 1 Change-Over (CO).
 SWITCHING TYPE: Momentary Function.
 LIGHT COLOUR: Green
 OPERATING TEMPERATURE: -20°C~+55°C.



LED VOLTAGE: 24V

MATERIALS:

CONTACT: Silver alloy.
 BASE: PBT.
 NUT: Nickel plated brass.

Art. Nr.

RND 210-00400

Specifications and Dimensions subject to change

