

## SPECIFICATIONS:

BUSHING:  $\varnothing 19\text{mm}$ .  
 CONTACT RATING: 5A @ 250VAC.  
 ELECTRICAL LIFE: 50,000 cycles at full load.  
 CONTACT RESISTANCE: 50m-ohms max. initial @2-4VDC.  
 INSULATION RESISTANCE: 1,000M-ohms min. @500VDC.  
 DIELECTRIC STRENGTH: 2,000V RMS 50~60Hz.  
 IP CLASS: IP65 protection.  
 TORQUE: 0.6Nm max. applied to nut.  
 OPERATING FORCE: 4N max.  
 CONSTRUCTION FORM: SPDT.  
 SWITCHING CIRCUIT: ON-MOM.  
 CONTACTS: 1 Break Contact (NC), 1 Make Contact (NO).  
 SWITCHING TYPE: Momentary Function.  
 LIGHT COLOUR: Red/Green  
 OPERATING TEMPERATURE:  $-20^{\circ}\text{C}\sim+55^{\circ}\text{C}$ .



LED VOLTAGE: 12V

## MATERIALS:

CONTACT: Silver alloy, plated in gold.  
 BASE: PBT.  
 NUT: Nickel plated brass.

Art. Nr.

**RND 210-00402**

## Specifications and Dimensions subject to change

