

Twist to Release Anti-Vandal Switch

SPECIFICATIONS:

BUSHING: $\varnothing 19\text{mm}$.
CONTACT RATING: 5A @ 250VAC.
ELECTRICAL LIFE: 50,000 cycles at full load.
CONTACT RESISTANCE: 50m-ohms max. initial @2-4VDC.
INSULATION RESISTANCE: 1,000M-ohms min.@500VDC.
DIELECTRIC STRENGTH: 2,000V RMS 50~60Hz.
IP CLASS: IP65 & IK02 protection.
TORQUE: 5~14Nm max. applied to nut.
OPERATING FORCE: 5.5~8N max.
CONSTRUCTION FORM: SPDT.
SWITCHING CIRCUIT: ON-ON.
SWITCHING TYPE: Turn to unlock.
OPERATING TEMPERATURE: $-25^{\circ}\text{C}\sim+55^{\circ}\text{C}$.



MATERIALS:

CONTACT: Silver alloy.
BASE: PA.
NUT: Nickel plated brass.

Art. Nr.
RND 210-00416

Specifications and Dimensions subject to change

