

Illuminated Anti-Vandal Buzzer

SPECIFICATIONS:

BUSHING: $\varnothing 19\text{mm}$.
CONTACT RATING: 30mA @ 12/24VDC.
SOUND TYPE: Flash buzz.
SOUND INTENSITY: $\geq 85\text{dB}$ at 0.1 meter away, $\geq 75\text{dB}$ at 1 meter away.
DIELECTRIC STRENGTH: 2,000V RMS 50~60Hz.
IP CLASS: IP40 & IK04 protection.
TORQUE: 5~14Nm max. applied to nut.
OPERATING TEMPERATURE: $-20^{\circ}\text{C} \sim +55^{\circ}\text{C}$.



MATERIALS:

BUSHING & BUTTON: Stainless steel.
BASE: PA.

Art. Nr.
RND 210-00428

Specifications and Dimensions subject to change

