

SPECIFICATIONS:

ELECTRICAL LIFE: 50,000 make-and-break cycles at full load.

CONTACT RESISTANCE: 10mΩ max. initial @2-4VDC 100mA for both silver and gold plated contacts.

INSULATION RESISTANCE: 1,000MΩ min.

DIELECTRIC STRENGTH: 1,500V RMS @ sea level.

OPERATING TEMPERATURE: -30°C to +85°C

MATERIALS:

CASE: Diallyl phthalate(DAP)(UL 94V-0)

TOGGLE HANDLE: Brass, chrome plated.


BUSHING: Brass, nickel plated.

HOUSING: Stainless Steel.

TERMINAL SEAL: Epoxy.


Art. Nr.

RND 210-00449




BUSHING

THD




PANEL MOUNTING



TERMINATION

PC THRU-HOLE



THK .030 [0.75]

ACTUATOR

