


SPECIFICATIONS:

ELECTRICAL LIFE: 50,000 make-and-break cycles at full load. CONTACT RESISTANCE: $10m\Omega$ max. initial @2-4VDC 100mA for both silver and gold plated contacts. INSULATION RESISTANCE: $1,000M\Omega$ min. DIELECTRIC STRENGTH: 1,500V RMS @ sea level. OPERATING TEMPERATURE: -30° C to $+85^{\circ}$ C

MATERIALS:

CASE: Diallyl phthalate(DAP)(UL 94V-0) TOGGLE HANDLE: Brass, chrome plated. BUSHING: Brass, nickel plated. HOUSING: Stainless Steel. TERMINAL SEAL: Epoxy.

Art. Nr. RND 210-00494



PANEL MOUNTING

