

SPECIFICATIONS:

ELECTRICAL LIFE: 50,000 make-and-break cycles at full load.

CONTACT RESISTANCE: 10mΩ max. initial @ 2-4VDC. 100mA for both silver and gold plated contacts.

INSULATION RESISTANCE: 1,000MΩ min.

DIELECTRIC STRENGTHS: 1,500V RMS @ sea level.

OPERATING TEMPERATURE: -30°C to +85°C.

MATERIALS:

CASE & BUSHING: PA9T.

ACTUATOR: Nylon, black std, internal o-ring sealed.

PANEL REAR MOUNT: Nylon, black std.

SWITCH SUPPORT: Brass, tin plated.

ACTUATOR PIVOT & MOUNTING BRACKET: Nylon, black std.

ACTUATOR PIVOT RETAINER: Stainless steel.

TERMINAL SEAL: Epoxy.

Art. Nr.

RND 210-00516

