

SPECIFICATIONS:

BUSHING: $\varnothing 19\text{mm}$.
CONTACT RATING: 5A @ 250VAC.
ELECTRICAL LIFE: 50,000 cycles at full load.
CONTACT RESISTANCE: 50m-ohms max. initial @2-4VDC.
INSULATION RESISTANCE: 1,000M-ohms min. @500VDC.
DIELECTRIC STRENGTH: 2,000V RMS 50~60Hz.
IP CLASS: IP67 protection.
TORQUE: 0.6Nm max. applied to nut.
OPERATING FORCE: 4N max.
CONSTRUCTION FORM: SPDT.
SWITCHING CIRCUIT: ON-ON.
CONTACTS: 1 Change-Over (CO).
SWITCHING TYPE: Momentary Function.
LIGHT COLOUR: Yellow
OPERATING TEMPERATURE: $-20^{\circ}\text{C}\sim+55^{\circ}\text{C}$.
LED Voltage: 24V

MATERIALS:

CONTACT: Silver alloy.
BASE: PBT.
NUT: Nickel plated brass.

Art. Nr.
RND 210-00555

Specifications and Dimensions subject to change

