



Specifications

Contact Rating	2A @ 36VDC
Electrical Life	200000 cycles
Contact Resistance	50 mohms max. (initial)
Insulation Resistance	1000 Mohms min. @ 500VDC
Dielectric Strength	2000V RMS 50~60Hz
Operating Temperature	-20°C ~ +70°C
Switching Circuit	OFF-MOM
IP Class	IP65
Torque	5~14Nm max. applied to nut
Operating Force	5.5N max.
Button Colour	Red

Materials

Bushing	Zinc alloy, black nickel plated
Contact	Silver alloy
Nut	Nickel plated brass
Button & Base	PBT

Art. Nr.

RND 210-00567

Specifications and Dimensions subject to change

