



Specifications

Contact Rating	1A @ 125VAC/250VAC
Electrical Life	5000 cycles
Mechanical Life	10000 cycles
Contact Resistance	30 mohms max.
Insulation Resistance	100 Mohms min. @ 500VDC
Dielectric Strength	1000VAC 1 min.
Operating Temperature	-20°C ~ +65°C
Switching Circuit	OFF-(ON)
Push Force	>3kg
Tolerance	+/- 0.3mm
Button Colour	Green
Terminal	Copper alloy, silver plated

Art. Nr.

RND 210-00579

Specifications and Dimensions subject to change

