# **Keylock Switch**



### Features

- Silver plated contacts and terminals
- Positive detent
- RoHS / REACH compliant
- Hex nut mounted


## Specification

Switching Configuration	1CO	
Current Rating	200 mA	
Contact Voltage	125 VAC	
Number of Positions	2 Positions (ON-ON)	
Number of Terminals	4 Terminals	
Contact Resistance	50 mOhm max.	
Insulation Resistance	100 MOhm min. (500 VDC)	
Dielectric Strength	800 VAC 1 min.	

## **Material Specification**

Housing and Cylinder	Die Cast Zinc Alloy, Nickel Plated
Keys	Zinc Alloy, Nickel Plated
Terminals	Silver Plated
Contacts	Silver Plated

### Drawing



KEY NO.

32.8