Test Lead 1.2 m, Red + Black



FEATURES:

Ø 2 mm safety measuring leads 2 pieces
Red/Black, 2 mm tip (with tip)
Comfort-grip
Safety-shrouded
Double insulated right-angle plug
UL listed lead wire:
Length: 48"(1.2m)
AWG: 18
Standard: EN 61010-031
Maximum rated voltage to earth and measuring category:
With push-on caps: CAT IV 600V, CAT III 1000V
Without push-on caps: CAT II 1000V
Maximum rated current: 10A



Art. Nr. RND 350-00004