4 mm Banana (female) Jack (socket) w/ 4 mm (male) Faston Terminal



Features

IP2X touchproof protection and double port


Applications

The safety design of this socket allows it to integrate easily the building of electrical equipments



Specification

Electrical protection	1000 V CAT II / 1000 V CAT III / 600 V CAT IV, reinforced insulation, pollution degree 1 or 2, up to 36 A
Operating Temperature Range	-20 °C+80 °C
Conductor Material	Brass
Weight	6 g
Colour	Black



The 4 mm banana female connection complies with the 4 mm banana plugs of most of the worldwide most famous manufacturers and meets the requirements of interchangeability dimensions of the French standard NF C 93-440:1986.

Plastic panel maximum thickness: 10.0 mm. Fastening:
•If hexagonal nut. Screwing by
14 mm open-end wrench.
Tightening torque, ≤ 2.3 N.m.

 If round nut Tightening torque, ≤ 2.3 N.m. Flat surface for antirotation purpose (if needed). Terminal: complying with 4.8 mm female Faston (and complying with lead-free tin soldering and 150 Watts maximum soldering iron).

RND Part Nr.

RND 350-00058